



47431912

## SCHUKO soc. out., S.1/B.3/B.7, red matt

### Technical properties

#### Architecture

|             |                        |
|-------------|------------------------|
| Design      | according to DIN 49440 |
| Fixing mode | flush-mounting         |

#### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

#### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 16 A     |

#### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

#### Dimensions

|   |       |
|---|-------|
| Insertion depth                         | 32 mm |
| Installation depth, flush-mounted boxes | 31 mm |

#### Cover, door

|       |                     |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

#### Materials

|                              |                     |
|------------------------------|---------------------|
| Design lines special colours | red                 |
| Colour                       | red                 |
| Colour                       | red                 |
| RAL colour                   | RAL 3003 - Ruby red |
| Material                     | thermoplastic       |
| Surface appearance           | matt                |
| Metallic colour              | No                  |

#### Installation, mounting

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

#### Connection

|                      |                          |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1  |
| Type of connection   | with plug-in terminals   |

#### Safety

|   |                                      |
|---|--------------------------------------|
| IK protection code against mechanical impacts | 05                                   |
| Protection index IP                           | IP20                                 |
| Protection                                    | without enhanced contact protection  |
| With enhanced contact protection              | No                                   |
| <b>Identification</b>                         |                                      |
| Main design line                              | Berker S.1/B.3/B.7                   |
| Secondary design line(s)                      | Berker S.1 ; Berker B.3 ; Berker B.7 |
| <b>Instructions</b>                           |                                      |
| Information text                              | Insert colour-coded.                 |