



47436013

SCHUKO soc. out., Q.x, green velvety

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Cover, door

Cover Central cover plate

Materials

Design lines special colours green

Surface appearance velvety

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free Yes

| | |
|----------------------------------|---|
| Protection | without enhanced contact protection |
| With enhanced contact protection | No |
| Identification | |
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
| Secondary design line(s) | Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9 |
| Instructions | |
| Information text | Insert colour-coded. |