



47436084

## SCHUKO socket outlet, Q.x, alu velvety, lacquered

### Technical properties

#### Architecture

Design according to DIN 49440

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Electric current

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

Metallic colour Yes

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

#### Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

|                                  |   |
|----------------------------------|---|
| Halogen free                     | No  |
| Protection                       | without enhanced contact protection               |
| With enhanced contact protection | No  |
| <b>Identification</b>            |   |
| Main design line                 | Berker Q.1/Q.3/Q.7/Q.9                            |
| Secondary design line(s)         | Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9 |