



47441606

**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,B3/7,ant.**

## Technical properties

### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

### Configuration

Number of modules	1
-------------------	---

### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

### Electric current

Rated current	16 A
---------------	------

### Cover, door

Hinged covers	when opening hinged cover, it can be arrested in end position
Cover	Central cover plate

### Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material	thermoplastic
Surface appearance	matt

### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

### Use

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps

<b>Safety</b>		
IK protection code against mechanical impacts		05
Protection index IP		IP20
REACH conform		Yes
RoHS conform		Yes
Halogen free		No
Protection	enhanced contact protection VDE 0620-1	
With enhanced contact protection		Yes

#### Identification

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7

#### Instructions

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	--