



47442045

**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,R.cl**

**Technical properties**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Cover, door**

Hinged covers with self-closing hinged covers

Cover Central cover plate

**Materials**

Colour of labelling 217,217,217

Colour of design line black

Material for printing PC-PMA black

Surface appearance glossy

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Settings**

Shading parameter R1\_czarny

Laser parameter R1\_schwarz

**Equipment**

Type of configuration Laserdruck

**Use**

---

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

---

Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps
--	--

---

**Safety**

---

REACH conform	Yes
---------------	-----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	Yes
--------------	-----

---

Protection	Enhanced contact protection
------------	-----------------------------

---

With enhanced contact protection	Yes
----------------------------------	-----

---

**Identification**

---

Main design line	Serie R.classic
------------------	-----------------

---

**Instructions**

---

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--

---

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	--