



47446089

SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,Q.x

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Cover, door

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	velvety
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps

Safety

IK protection code against mechanical impacts	02
Protection index IP	IP20
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

Instructions

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	--