



47452045

SCHUKO soc. out., mounting orient. var. in 45° steps, R.classic, black glossy

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black
Surface appearance	glossy
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Equipment

Type of configuration	Laserdruck
-----------------------	------------

Use

Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps
--	--

Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Protection	without enhanced contact protection
------------	-------------------------------------

With enhanced contact protection	No
----------------------------------	----

Identification

Main design line	Serie R.classic
------------------	-----------------