



SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,K5,steel

Technical properties

| Architecture | |
|--|---|
| Design | according to DIN 49440 |
| Configuration | |
| Number of modules | 1 |
| Main electrical features | |
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Frequency | 50/60 Hz |
| Rated current | 16 A |
| Electric current | |
| Rated current | 16 A |
| Dimensions | |
| Installation depth, flush-mounted boxes | 35 mm |
| Cover, door | |
| Hinged covers | when opening hinged cover, it can be arrested in end position |
| Cover | Central cover plate |
| Materials | |
| Colour of design line | Stainless steel |
| Material / workmanship | metal, matt finish |
| Surface appearance | matt |
| Metallic colour | Yes |
| Installation, mounting | |
| Installation mode | with spreader claws |
| Connection | |
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1 |
| Type of connection | with plug-in terminals |
| Use | |
| Differentiation characteristic 2 - Sales | enhanced contact protection |
| Differentiation characteristic 3 - Sales | Mounting orientation variable in 45° steps |

Safety

| IK protection code against mecanical impacts | 07 |
|--|--|
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |
| Protection | enhanced contact protection VDE 0620-1 |
| With enhanced contact protection | Yes |
| Identification | |
| Main design line | Berker K.5 |