



47477109

**SCHUKO soc. out. hinged cover, enhanced contact prot., K.1, p. white glossy**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Cover, door**

Hinged covers	when opening hinged cover, it can be arrested in end position
Cover	Central cover plate

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	glossy
Metallic colour	No

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps

**Safety**

---

IK protection code against mechanical impacts	05
Protection index IP	IP20
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

**Identification**

---

Main design line	Berker K.1
------------------	------------

**Instructions**

---

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	--