



47487104

**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,K5,steel**

**Technical properties**

**Architecture**

|             |                        |
|-------------|------------------------|
| Design      | according to DIN 49440 |
| Fixing mode | flush-mounting         |

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Main electrical features**

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 16 A     |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Dimensions**

|                 |       |
|-----------------|-------|
| Insertion depth | 32 mm |
|-----------------|-------|

**Cover, door**

|               |   |
|---------------|---|
| Hinged covers | when opening hinged cover, it can be arrested in end position |
| Cover         | Central cover plate   |

**Materials**

|                        |                             |
|------------------------|-----------------------------|
| Colour of design line  | Stainless steel             |
| Colour                 | stainless steel             |
| Colour                 | stainless steel optics      |
| RAL colour             | RAL 9022 - Pearl light grey |
| Material / workmanship | metal, matt finish          |
| Material               | stainless steel             |
| Surface appearance     | matt                        |

**Installation, mounting**

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

**Connection**

|                      |                          |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1  |
| Type of connection   | with plug-in terminals   |

**Use**

---

|  |  |
|--|--|
| Differentiation characteristic 1 - Sales | Labelling field                            |
| Differentiation characteristic 2 - Sales | enhanced contact protection                |
| Differentiation characteristic 3 - Sales | Mounting orientation variable in 45° steps |

---

**Safety**

---

|   |                             |
|---|-----------------------------|
| IK protection code against mechanical impacts | 07                          |
| Protection index IP                           | IP20                        |
| Protection                                    | Enhanced contact protection |
| With enhanced contact protection              | Yes                         |

---

**Identification**

---

|                  |            |
|------------------|------------|
| Main design line | Berker K.5 |
|------------------|------------|

---

**Instructions**

---

|                  |  |
|------------------|--|
| Information text | Labelling field height arranged for 6 mm P-touch strips. Specially suited to combinations of several socket outlets if right angle plugs are used. |
|------------------|--|

---