



47487109

SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,K1

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Hinged covers	when opening hinged cover, it can be arrested in end position
Cover	Central cover plate

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 1 - Sales	Labelling field
--	-----------------

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps
--	--

Safety

IK protection code against mechanical impacts	05
---	----

Protection index IP	IP20
---------------------	------

Protection	enhanced contact protection VDE 0620-1
------------	--

With enhanced contact protection	Yes
----------------------------------	-----

Identification

Main design line	Berker K.1
------------------	------------

Instructions

Information text	Labelling field height arranged for 6 mm P-touch strips. Specially suited to combinations of several socket outlets if right angle plugs are used.
------------------	--