



47491909

SCHUKO soc. out., enhncd contact prot., S.1/B.3/B.7, p. white, matt, plastic

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 1 - Sales

with labelling field

Differentiation characteristic 2 - Sales

enhanced contact protection

Safety

IK protection code against mechanical impacts

05

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

Identification

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1, Berker B.3, Berker B.7

Instructions

Information text

Labelling field height arranged for P-touch strips 6 mm.