



47498989

SCHUKO soc. out., enhncd contact prot., S.1/B.3/B.7, p. white glossy

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 1 - Sales with labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

Safety

| | |
|---|-----------------------------|
| IK protection code against mechanical impacts | 02 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| Protection | Enhanced contact protection |
| With enhanced contact protection | Yes |

Identification

| | |
|--------------------------|--------------------------------------|
| Main design line | Berker S.1/B.3/B.7 |
| Secondary design line(s) | Berker S.1 ; Berker B.3 ; Berker B.7 |

Instructions

| | |
|------------------|--|
| Information text | Labelling field height arranged for P-touch strips 6 mm. |
|------------------|--|
