



47501902

## SCHUKO soc. out., S.1/B.3/B.7, red matt

### Technical properties

#### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

#### Electric current

Rated current	16 A
---------------	------

#### Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

#### Cover, door

Cover	Central cover plate
-------	---------------------

#### Materials

Design lines special colours	red
Colour	red
Colour	red
RAL colour	RAL 3003 - Ruby red
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

#### Use

**Safety**

IK protection code against mechanical impacts	05
Protection index IP	IP20
RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection
With enhanced contact protection	No

**Identification**

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7

**Instructions**

Information text	Insert colour-coded. 1140. Labelling field height designed for 6 mm P-touch strips.
------------------	---