



47501903

**SCHUKO soc. out., S.1/B.3/B.7, green matt**

**Technical properties**

**Architecture**

|             |                        |
|-------------|------------------------|
| Design      | according to DIN 49440 |
| Fixing mode | flush-mounting         |

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Main electrical features**

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 16 A     |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Dimensions**

|   |       |
|---|-------|
| Insertion depth                         | 32 mm |
| Installation depth, flush-mounted boxes | 31 mm |

**Cover, door**

|       |                     |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

**Materials**

|                              |                       |
|------------------------------|-----------------------|
| Design lines special colours | green                 |
| Colour                       | green                 |
| Colour                       | green                 |
| RAL colour                   | RAL 6029 - Mint green |
| Material                     | thermoplastic         |
| Surface appearance           | matt                  |
| Metallic colour              | No                    |

**Installation, mounting**

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

**Connection**

|                      |                          |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1  |
| Type of connection   | with plug-in terminals   |

**Use**

**Safety**

---

|   |                                     |
|---|-------------------------------------|
| IK protection code against mechanical impacts | 05                                  |
| Protection index IP                           | IP20                                |
| REACH conform                                 | Yes                                 |
| RoHS conform                                  | Yes                                 |
| Halogen free                                  | No                                  |
| Protection                                    | without enhanced contact protection |
| With enhanced contact protection              | No                                  |

**Identification**

---

|                          |                                      |
|--------------------------|--------------------------------------|
| Main design line         | Berker S.1/B.3/B.7                   |
| Secondary design line(s) | Berker S.1 ; Berker B.3 ; Berker B.7 |

**Instructions**

---

|                  |   |
|------------------|---|
| Information text | Insert colour-coded. 1140. Labelling field height designed for 6 mm P-touch strips. |
|------------------|---|