



47501915

**SCHUKO soc. out. "EDV" imprint, S.1/B.3/B.7, red matt**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Design lines special colours	red
Colour	red
Colour	red
RAL colour	RAL 3003 - Ruby red
Material	thermoplastic
Surface appearance	matt

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales	Labelling field
--	-----------------

<b>Safety</b>		
IK protection code against mechanical impacts		05
Protection index IP		IP20
RoHS conform		Yes
Halogen free		No
Protection	without enhanced contact protection	
With enhanced contact protection		No

#### Identification

Main design line	Berker S.1/B.3/B.7	
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7	

#### Instructions

Information text	Insert colour-coded. ; Labelling field height arranged for P-touch strips 6 mm.	
------------------	---	--