



47506086

**SCHUKO soc. out., Q.x, ant. velvety, lacq.**

#### Technical properties

##### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Electric current

Rated current	16 A
---------------	------

##### Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	duroplastic
Surface appearance	velvety
Metallic colour	No

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales

with labelling field

**Safety**

IK protection code against mechanical impacts

02

Protection index IP

IP20

Protection

without enhanced contact protection

With enhanced contact protection

No

**Identification**

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

**Instructions**

Information text

Labelling field height arranged for P-touch strips 6 mm.