



47508989

SCHUKO soc. out., S.1/B.3/B.7, p. white glossy

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	duroplastic
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Safety

IK protection code against mechanical impacts	02
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Protection	without enhanced contact protection
With enhanced contact protection	No

Identification

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7

Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--