



47512045

## SCHUKO soc. out. hinged cover, enhanced contact prot., R.1/R.3, black glossy

### Technical properties

#### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

#### Electric current

Rated current	16 A
---------------	------

#### Cover, door

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

#### Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

#### Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

**Equipment**

Type of configuration

Laserdruck

**Use**

Differentiation characteristic 2 - Sales

enhanced contact protection

**Safety**

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

**Identification**

Application, usage

Flush-mounted wet-room installation

Main design line

Berker R.1/R.3/R.8

Secondary design line(s)

Berker R.1, Berker R.3, Berker R.8

**Instructions**

Special note text

these marked articles (see symbol) are only suitable for the water-protected flush-mounted installation IP44 in conjunction with the corresponding seal, frame and contact protection box (imprint "IP44").