



47516064

SCHUKO socket outlet with hinged cover, Q.x, alu velvety, lacquered

Technical properties

Architecture

| | |
|-------------|------------------------|
| Design | according to DIN 49440 |
| Fixing mode | flush-mounting |

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Frequency | 50/60 Hz |
| Rated current | 16 A |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Cover, door

| | |
|---------------|-----------------------------------|
| Hinged covers | with hinged cover that falls back |
| Cover | Central cover plate |

Materials

| | |
|--------------------|----------------------------|
| Colour | aluminium |
| Colour | aluminium optics |
| RAL colour | RAL 9006 - White aluminium |
| Material | thermoplastic |
| Surface appearance | velvety |
| Metallic colour | Yes |

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

Connection

| | |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1 |
| Type of connection | with plug-in terminals |

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | 02 |
| Protection index IP | IP20 |
| REACH conform | Yes |

| | |
|----------------------------------|--|
| RoHS conform | Yes |
| Halogen free | No |
| Protection | without enhanced contact protection |
| With enhanced contact protection | No |
| Identification | |
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
| Secondary design line(s) | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9 |