



47516084

## SCHUKO socket outlet with hinged cover, Q.x, alu velvety, lacquered

### Technical properties

#### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

#### Electric current

Rated current	16 A
---------------	------

#### Cover, door

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

#### Materials

Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety
Metallic colour	Yes

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

#### Use

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

#### Safety

IK protection code against mechanical impacts	02
Protection index IP	IP20
Protection	Enhanced contact protection
With enhanced contact protection	Yes

#### Identification

Application, usage	Flush-mounted wet-room installation
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

#### Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).
-------------------	--