



47516084

SCHUKO socket outlet with hinged cover, Q.x, alu velvety, lacquered

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Cover, door

Hinged covers with hinged cover that falls back

Cover Central cover plate

Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

Metallic colour Yes

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 2 - Sales enhanced contact protection

Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

| | |
|----------------------------------|-----------------------------|
| Halogen free | No |
| Protection | Enhanced contact protection |
| With enhanced contact protection | Yes |

Identification

| | |
|--------------------------|---|
| Application, usage | Flush-mounted wet-room installation |
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
| Secondary design line(s) | Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9 |

Instructions

| | |
|-------------------|--|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200). |
|-------------------|--|