



47517103

SCHUKO soc. out. hinged cover, enhncd contact prot., K.5, al., al. anodised

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	35 mm
-----------------------------------------	-------

Cover, door

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

Materials

Colour of design line	Aluminium
Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	aluminium, anodised
Material	Aluminium
Surface appearance	matt
Metallic colour	Yes

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 2 - Sales

enhanced contact protection

Safety

IK protection code against mechanical impacts

07

Protection index IP

IP20

Protection

enhanced contact protection VDE 0620-1

With enhanced contact protection

Yes

Identification

Main design line

Berker K.5