



47517109

SCHUKO soc. out. hinged cover, enhanced contact prot., K.1, p. white glossy

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Cover, door

Hinged covers with hinged cover that falls back

Cover Central cover plate

Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 2 - Sales enhanced contact protection

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform	Yes
Halogen free	Yes
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

Identification

Main design line	Berker K.1
------------------	------------