



47517206

**SCHUKO soc. out. hinged cover, enhncd contact prot., K.1, ant. matt, lacq.**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Cover, door**

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

**Materials**

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

**Safety**

---

IK protection code against mechanical impacts	05
Protection index IP	IP20
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

---

**Identification**

---

Application, usage	Flush-mounted wet-room installation
Main design line	Berker K.1

---

**Instructions**

---

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).
-------------------	--

---