



475501

**SCHUKO soc.out.,enhncd contact prot.,mounting orient. var. in 45°step,1930/glass**

## Technical properties

### Architecture

Design according to DIN 49440

### Configuration

Number of modules 1

### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

### Electric current

Rated current 16 A

### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

### Cover, door

Cover Central cover plate

### Materials

Colour of design line black

Surface appearance glossy

Metallic colour No

### Installation, mounting

Installation mode with spreader claws

### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Mounting orientation variable in 45° steps

### Safety

IK protection code against mechanical impacts 02

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
With enhanced contact protection	Yes
<b>Identification</b>	
Main design line	Serie 1930/Glas
Secondary design line(s)	Serie 1930 ; Serie 1930 Porzellan Made by Rosenthal ; Serie Glass