



5031

Rocker push-button NO contact Module insert

Technical properties

Architecture

Type of control unit rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode Normally open contact

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 30 mm

Contact spacing > 3 mm

Height 70.8 mm

Width 70.8 mm

Materials

Material Plastic/metal

Installation, mounting

Installation mode with spreader claws

Connection

Conductor cross-section (rigid) 2.5

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Scope of delivery

With lamp No

Equipment

Quantity of NC contacts	0
-------------------------	---

Quantity of NO contacts	1
-------------------------	---

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

Use cases

Application	Barrier-free application, HVAC-control, Light control
-------------	---

Safety

Protection index IP	IP20
---------------------	------

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Light control
------------------	---------------

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--