



503150

Push-button, NO contact for installation in hollow walls, Module inserts

Technical properties

Architecture

Type of control unit rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode Normally open contact

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 19.5 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode low installation depth ; without spreader claws ; for screw fastening

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Scope of delivery

With lamp No

Equipment

Quantity of NC contacts 0

Quantity of NO contacts 1

Lighting for lighting and monitoring circuit

Use cases

| | |
|-------------|---|
| Application | Barrier-free application ; HVAC-control ; Light control |
|-------------|---|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

Identification

| | |
|--------------------|------------------------------|
| Application, usage | HVAC control ; Light control |
|--------------------|------------------------------|

| | |
|------------------|---------------|
| Main design line | Light control |
|------------------|---------------|