



503150

Push-button, NO contact for installation in hollow walls, Module inserts

Technical properties

Architecture

Type of control unit rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode Normally open contact

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 19.5 mm

Height 71 mm

Width 71 mm

Materials

Material Plastic/metal

Installation, mounting

Installation mode low installation depth ; without spreader claws ; for screw fastening

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Scope of delivery

With lamp No

Equipment

Quantity of NC contacts	0
Quantity of NO contacts	1
Lighting	for lighting and monitoring circuit
Use cases	
Application	Barrier-free application ; HVAC-control ; Light control
Safety	
Protection index IP	IP20
Identification	
Application, usage	HVAC control ; Light control
Main design line	Light control