



503404

**Group push-button, 4NO contacts, comm. input terminal, neut. pos., light control**

**Technical properties**

**Architecture**

Type of control unit double rocker

**Configuration**

Switch mode with neutral position

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Momentary-contact current 10 A

**Dimensions**

Depth 41.6 mm

Contact spacing > 3 mm

Height 71 mm

Width 71 mm

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

**Equipment**

Lighting for illumination

**Use cases**

Application Blind control ; Light control

**Use**

Differentiation characteristic 3 - Sales with neutral-position

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

---

**Identification**

Application, usage	Light control
Main design line	Light control

---

**Instructions**

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	------------------------------------------------------------------