



5035

## Series push-button 2 NO contacts with common input terminal

### Technical properties

#### Architecture

Type of control unit double rocker

#### Functions

Switching angle 3.5 °

#### Configuration

Switch mode 2 NO, common input terminal

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 41.6 mm

Insertion depth 32.3 mm

Height 70.8 mm

Width 70.8 mm

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

#### Scope of delivery

With lamp No

#### Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Lighting for illumination

---

**Use cases**

---

Application	Light control
-------------	---------------

---

**Safety**

---

REACH conform	Yes
---------------	-----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	Yes
--------------	-----

---

**Identification**

---

Application, usage	Light control
--------------------	---------------

---

Main design line	Light control
------------------	---------------

---

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--