



503520

Blind push-button 1pole, blind control

Technical properties

Architecture

Type of control unit	double rocker
----------------------	---------------

Functions

Switching angle	3.5 °
-----------------	-------

Configuration

Switch mode	with mechanical and electrical interlock to prevent mutual activation
-------------	---

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V
Frequency	50/60 Hz

Electric current

Momentary-contact current	10 A
---------------------------	------

Dimensions

Depth	42 mm
Insertion depth	31.2 mm
Height	70.8 mm
Width	70.8 mm

Materials

Material	Plastic/metal
----------	---------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of connection	with plug-in terminals
--------------------	------------------------

Use cases

Application	Blind control
-------------	---------------

Safety

Protection index IP	IP20
REACH conform	Yes

RoHS conform	Yes
Halogen free	Yes
Identification	
Application, usage	Blind control
Main design line	Blind control