



5101

Push-button and pilot lamp E10 module inserts

Technical properties

Configuration

Switch mode Normally open contact

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 2 A

Dimensions

Depth 30.4 mm

Insertion depth 29.3 mm

Height 71 mm

Width 71 mm

Materials

Material Plastic/metal

Incandescent bulbs control

Incandescent lamp power max. 2 W

Connection

Type of connection with screw terminals

Equipment

Lighting for lighting and monitoring circuit

Use cases

Application Light control

Safety

Protection index IP IP20

Identification

Application, usage Light control

Main design line Light control