



5101

Push-button and pilot lamp E10 module inserts

Technical properties

Configuration

Switch mode	Normally open contact
-------------	-----------------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Momentary-contact current	2 A
---------------------------	-----

Dimensions

Depth	30.4 mm
Insertion depth	29.3 mm
Height	71 mm
Width	71 mm

Incandescent bulbs control

Incandescent lamp power	max. 2 W
-------------------------	----------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

Use cases

Application	Light control
-------------	---------------

Identification

Application, usage	Light control
Main design line	Light control