



51019909

**Push-button complete f. stairway light, screw term., S.1, p.white, matt, plastic**

**Technical properties**

**Architecture**

Type of control unit single push button

**Configuration**

Switch mode Normally open contact

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Momentary-contact current 2 A

**Dimensions**

Depth 47.5 mm

Insertion depth 28.2 mm

Height 81 mm

Width 81 mm

**Materials**

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance matt

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Type of connection with screw terminals

**Scope of delivery**

Component with insert, frame, centre plate and red button

**Equipment**

Lighting without neon lamp

**Use cases**

Application

Light control

---

**Use**

Differentiation characteristic 3 - Sales

with screw terminals

---

**Safety**

REACH conform

Yes

RoHS conform

Yes

---

**Identification**

Main design line

Berker S.1