



51019909

**Push-button complete f. stairway light, screw term., S.1, p.white, matt, plastic**

#### Technical properties

##### Architecture

Type of control unit single push button

##### Configuration

Switch mode Normally open contact

Antibacterial treatment No

##### Compatibility

IFTTT support available No

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

##### Electric current

Momentary-contact current 2 A

##### Dimensions

Depth 47.5 mm

Insertion depth 28.2 mm

Height 81 mm

Width 81 mm

##### Materials

Colour of design line polar white

Colour polarwhite

Colour white

RAL colour RAL 9010 - Pure white

Material thermoplastic

Surface appearance matt

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Type of connection with screw terminals

##### Scope of delivery

Component with insert, frame, centre plate and red button

##### Equipment

Lighting	without neon lamp
<b>Use cases</b>	
Application	Light control
<b>Use</b>	
Differentiation characteristic 3 - Sales	with screw terminals
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
<b>Identification</b>	
Main design line	Berker S.1