



52031

Floodlight 400W PIR 140° Black

Technical properties

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Length	27 m
--------	------

Power

Halogen switching capacity 230V	0 / 500 W
---------------------------------	-----------

Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

Detection

Detection angle	140 °
-----------------	-------

Materials

Colour	black
--------	-------

Lighting control

Brightness measurement range	5 / 2000 Lux
------------------------------	--------------

Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

Settings

Time delayed range	5s / 5min
--------------------	-----------

Safety

Protection class	isol.class I
------------------	--------------

Use conditions

Operating temperature	-20...50 °C
Storage/transport temperature	-20...60 °C