



52035

Floodlight 120W PIR 140° Black

Technical properties

Architecture

Fixing mode surface-mounting

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50 Hz

Dimensions

Length 20 m

Power

Halogen switching capacity 230V 0 / 150 W

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 140 °

Materials

Colour black

Lighting control

Brightness measurement range 5 / 2000 Lux

Settings

Time delayed range 5s / 5min

Safety

Protection class isol.class I

Use conditions

Operating temperature -20...50 °C

Storage/transport temperature -20...60 °C