



52045

Bulkhead 60W PIR 110°

Technical properties

Main electrical features

Rated operational voltage U _e	230 V
Rated voltage	230 V
Type of supply voltage	AC
Frequency	50 Hz

Dimensions

Height of installed product	250 mm
Length	110 mm
Built-in width	0 mm

Power

Incandescent bulb power	60 W
-------------------------	------

Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

Detection

Detection angle	110 °
-----------------	-------

Materials

Colour	white
RAL colour	RAL 9010 - Pure white

Installation, mounting

Suitable for ground mounting	No
------------------------------	----

Safety

Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-20...50 °C
Storage/transport temperature	-20...60 °C