



## Bulkhead 60W PIR 110°

## **Technical properties**

Rated operational voltage Ue	230 V
Rated voltage	230 V
Type of supply voltage	AC
Frequency	50 Hz
Dimensions	
Height of installed product	250 mm
Length	110 m
Built-in width	0 mm
Power	
Incandescent bulb power	60 W
Power supply	
Supply voltage	230 V +10% / -15%

## Detection angle 110 °

Materials	
Colour	white
RAL colour	RAL 9010 - Pure white

Installation, mounting	
Suitable for ground mounting	No

Safety	
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Use conditions	

Operating temperature	-2050 °C
Storage/transport temperature	-2060 °C