



52545

Floodlight 120W PIR 200° Black

Technical properties

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50 Hz

Dimensions

Built-in width 0 mm

Power

Halogen switching capacity 230V 0 / 150 W

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 200 °

Materials

Colour black

Lighting control

Brightness measurement range 5 / 2000 Lux

Connection

Connection type 1 to 1,5 mm²

Settings

Time delayed range 5s / 5min

Safety

Protection class isol.class I

Use conditions

Operating temperature -20...50 °C

Storage/transport temperature -20...60 °C