



53420211

**Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.**

### Technical properties

#### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	13 A

#### Cover, door

Cover	Central cover plate
-------	---------------------

#### Materials

Colour of design line	brown
Colour	brown
Colour	brown
RAL colour	RAL 8011 - Nut brown
Material	thermoplastic

#### Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

#### Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw terminals

#### Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	with screw terminals

#### Safety

IK protection code against mechanical impacts	IK02
Protection	Enhanced contact protection
With enhanced contact protection	Yes

#### Identification

