



53420216

Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.

Technical properties

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 13 A

Cover, door

Cover Central cover plate

Materials

Colour independent of design lines anthracite

Surface appearance glossy

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Connection terminals according to IEC 60884-1

Type of connection with screw terminals

Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales with screw terminals

Safety

IK protection code against mechanical impacts IK02

Protection Enhanced contact protection

With enhanced contact protection Yes

Identification

Main design line Berker Q.1/Q.3/Q.7/Q.9