



53420219

**Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.**

## Technical properties

### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

### Configuration

Number of modules	1
-------------------	---

### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	13 A

### Cover, door

Cover	Central cover plate
-------	---------------------

### Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic

### Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

### Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw terminals

### Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	with screw terminals

### Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes
Protection	Enhanced contact protection
With enhanced contact protection	Yes

