



613036

Change-over switch for installation in hollow walls, Module inserts

Technical properties

Architecture

Type of control unit single rocker

Configuration

Switch mode Off/change-over

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 70.8 mm

Width 70.8 mm

Materials

Surface appearance other

Installation, mounting

Installation mode low installation depth ; without spreader claws

Connection

Type of connection with plug-in terminals

Type of connection Quickconnect

Equipment

Lighting can be illuminated using neon and glow lamp unit with N-terminal ; for lighting and monitoring circuit

Heating switch No

Use cases

Application

Light control ; Barrier-free application

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

Identification

Application, usage	Light control
Main design line	Light control