



6161036084

Socket outlet without earthing contact, Q.x, alu velvety, lacquered

Technical properties

Architecture

Fixing mode	flush-mounting
Number of poles	2pole

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm
Mirror depth	8 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	aluminium
Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	duroplastic
Surface appearance	velvety
Metallic colour	Yes

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw terminals

Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

Safety

IK protection code against mechanical impacts	02
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection

Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
