



6161036084

## Socket outlet without earthing contact, Q.x, alu velvety, lacquered

### Technical properties

#### Architecture

Fixing mode	flush-mounting
Number of poles	2pole

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

#### Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm
Mirror depth	8 mm

#### Cover, door

Cover	Central cover plate
-------	---------------------

#### Materials

Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	duroplastic
Surface appearance	velvety
Metallic colour	Yes

#### Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

#### Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw terminals

#### Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

#### Safety

IK protection code against mechanical impacts	02
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection
<b>Identification</b>	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9