



6167038982

**Soc. out. out earthing contact, S.1, white glossy**

**Technical properties**

**Architecture**

Number of poles 2pole

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

Mirror depth 8 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line white

Colour white

Colour white

Surface appearance glossy

**Installation, mounting**

Installation mode without spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Type of connection with plug-in terminals

**Safety**

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Protection without enhanced contact protection

**Identification**

