



6167331404

Soc. out. out earthing contact, enhncd contact prot., B.7, al., matt, lacq.

Technical properties

Architecture

Number of poles 2pole

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Dimensions

Insertion depth 32 mm

Mirror depth 8 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance matt

Installation, mounting

Installation mode without spreader claws

Connection

Connection terminals according to IEC 60884-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection Enhanced contact protection

Identification

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7