



6167331404

**Soc. out. out earthing contact, enhncd contact prot., B.7, al., matt, lacq.**

#### Technical properties

##### Architecture

Number of poles 2pole

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

Mirror depth 8 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance matt

##### Installation, mounting

Installation mode without spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Type of connection with plug-in terminals

##### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

##### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection Enhanced contact protection

**Identification**

---

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7